



HX-480HL is a low profile copper core radiator designed for four 120mm fans. With a fin density of 11 FPI (fins per inch), it is optimized for quieter air flow ranges. It has a dual pass coolant design, and is G 1/4 BSPP (parallel) thread for hose fittings. 30mm (1.18") long mounting screws are included for 25mm thick fans (see Koolance [radiator screw packs](#) for additional options).

General	
Weight	3.50 lb (1.59 kg)
Wetted Materials	Brass/Copper
Radiators	
Fan Capacity	4 x 120
Fins Per Inch (FPI)	11