



The new RM2 series offers greater performance over RM1 systems. Koolance's rack-optimized systems eliminate the need for airflow over sensitive electronic hardware, ideal for manufacturing areas and other applications in high-dust environments. Choose hardware at will with the assurance they'll be kept clean, cool, and quiet. You might even reduce power consumption by eliminating chassis and chip fans!

- Rack-mountable 4U IPC form factor
- 340W heat dissipation potential
- Lockable front door for security
- 2 front USB ports
- Heavy-duty steel construction

General	
Weight	39.00 lb (17.69 kg)
Cooling Systems	
Display Type	LED
Fans	4 x 80mm (168CFM)
Max Flow Rate (10-13mm ID)	R-PMP01
Power Source	12 VDC
Radiator	Aluminum
Temperature Sensors	55K Thermistor

