



Koolance swiveling G 1/4 BSP socket fitting with a 45-degree bend.

General	
Weight	0.06 lb (0.03 kg)
Fitting Thread	G 1/4 BSP
Max Pressure Tolerance @ 25° C	8kgf/cm ² (113.8psi)
Max Temperature Tolerance	100° C (212° F)
Wetted Materials	Brass, Nickel Plating, EPDM

