www.koolance.com

Specifications Sheet

Generated: 2026-10-31

P/N: ADT-DXG60-BK


Fitting Single, *Black* Swiveling 60-Degree, G 1/4 BSPP



Koolance swiveling G 1/4 BSPP socket fitting. Each segment rotates for a maximum 60-degree bend.

General	
Weight	0.09 lb (0.04 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	8kgf/cm2 (113.8psi)
Max Temperature Tolerance	100°C (212°F)
Wetted Materials	Brass, EPDM

File



NO.	DESCRIPTION				MATER'L		QUANTITY	REMARKS
KOOLANCE					UNIT	MM	APPAR ADT-DXG60	
	BY	BY	BY	APPRO BY	SCALE	N/S	TITLE Ass'y	
DATE					3RD ANGLE			
04/06/2017	S.J.LEE				CODE NO.		DWG. NO.	