www.koolance.com

Specifications Sheet

Generated: 2026-11-09

P/N: ADT-DXG90S-BK


Fitting Single, *Black* Swiveling 90-Degree (Low Profile), G 1/4 BSPP





Koolance low profile swiveling G 1/4 BSPP socket fitting. Each segment rotates for a maximum 90-degree bend.

General	
Weight	0.09 lb (0.04 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	8kgf/cm2 (113.8psi)
Max Temperature Tolerance	100°C (212°F)
Wetted Materials	Brass, EPDM

File







NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT MM	APPAR ADT-DXG90S(-BK)	
	BY	BY	BY	APPRO. BY	SCALE N/S	TITLE Ass'y	
DATE					3RD ANGLE		
JUN.15.2022	S.J.LEE				CODE NO.	DWG. NO.	