

**Aquian ICM-505 Compact Liquid Cooling System [06mm, 1/4in]**



Keep your favorite case with the Koolance Aquian! An all-in-one liquid cooling system, it's designed to provide quick and easy installation inside an ATX chassis. The Aquian mounts to a standard rear 120mm fan grill, and features a 90° hinged design for easy installation and maintenance.

A CPU-305-H06 Cooler is **included** with brackets for: AMD Athlon 64, FX, Opteron, Sempron, Athlon XP, Duron, Intel P-4 (LGA-775 and 478), and Celeron processors. Xeon CPUs require an additional adapter.

The Koolance Aquian ICM-505 is powerful for its size, performing similar to an Exos-AI. It combines a full-sized radiator, dual pump reservoir, and control board in an aluminum chassis. A 3.5" LED temperature display is included, which could alternatively be adapted to a 5.25" bay.

- 120mm fan (included) auto-adjusts for quiet operation, or select from 10 manual speeds
- Built-in safety alarm and automatic shutdown mode is configurable
- 3.5" LED temperature display with controls
- LED reservoir lighting
- Hinged design for easy system access
- Fan bracket adjusts to mount different grill positions
- Top reservoir refill plug
- Uses 12V connection from computer power supply
- Rotational liquid fittings


NOTE: The Aquian ICM-505 is designed for ATX chassis with a rear 120mm fan grill. For 80mm grills, it may still work with the Koolance grill adapter. The fan bracket will adjust up to 1 inch (2.5cm) vertically to accommodate different grill locations, and to help avoid potential conflicts between the fittings and longer video cards. The Aquian ICM-505 can not be mounted upside-down.

**Intended Tubing Size**

**ID:** 6mm (1/4")

**OD:** 10mm (3/8")

**Wall:** 2mm (5/64")



General	
Weight	10.00 lb (4.54 kg)
Cooling Systems	
Display Type	LED
Fans	1 x 120mm (90CFM)
Max Flow Rate (10-13mm ID)	R-PMP01
Power Source	12 VDC
Radiator	Aluminum
Temperature Sensors	55K Thermistor