

**Coolant Temperature Sensor Plug, K-Type
Thermocouple**

Coolant K-type thermocouple sensor, compatible with Koolance EXC and ALX series systems. Sensor fitting is G 1/4 BSPP (parallel) threaded. Wire length = 38" (965mm). Accuracy = $\pm 1.5^{\circ}\text{C}$, temperature range = -40 to 120°C (-40 to 248°F).

| General | |
|-------------------------------|---|
| Weight | 0.04 lb (0.02 kg) |
| Fitting Thread | G 1/4 BSPP |
| Materials | Nickel-Plated Brass, Stainless Steel, EPDM |
| Max Temp. Operating Tolerance | 120°C (248°F) |