



CPU-370SA is a lighter weight, lower priced version of Koolance's acclaimed CPU-370 water block. It includes a similar nickel-plated copper microfin cold plate (0.25mm fins, 0.30mm channels), o-ring sealed impingement plate, and a solid acetal top designed for AMD sockets.

Standard G 1/4 BSPP threading will accept any Koolance fitting diameter up to 19mm (3/4in) OD compression style. Please select the desired fitting type for this base model (it does not include fittings).

The CPU-370SA supports most boards using the following processors:

- AMD socket AM2, AM2+, AM3, AM3+, FM1, FM2
- AMD socket 1207(F)/C32, 939, 940 (with separate [BKT-CP021K](#))
- AMD socket G34 (with separate [BLT-CPAMDG34](#))

General	
Weight	0.38 lb (0.17 kg)
Materials	Nickel-Plated Copper, Stainless Steel, POM Acetal, EPDM