www.koolance.com

Specifications Sheet

Generated: 2026-11-12

P/N: CPU-370SA

CPU-370SA Water Block (AMD Processor)



CPU-370SA is a lighter weight, lower priced version of Koolance's acclaimed CPU-370 water block. It includes a similar nickel-plated copper microfin cold plate (0.25mm fins, 0.30mm channels), o-ring sealed impingement plate, and a solid acetal top designed for AMD sockets.

Standard G 1/4 BSPP threading will accept any Koolance fitting diameter up to 19mm (3/4in) OD compression style. Please select the desired fitting type for this base model (it does not include fittings).

The CPU-370SA supports most boards using the following processors:

- AMD socket AM2, AM2+, AM3, AM3+, FM1, FM2
- AMD socket 1207(F)/C32, 939, 940 (with separate BKT-CP021K)
- AMD socket G34 (with separate BLT-CPAMDG34)

General	
Weight	0.38 lb (0.17 kg)
Wetted Materials	Nickel-Plated Copper, Stainless Steel, POM Acetal, EPDM