



www.koolance.com

Specifications Sheet

Generated: 2025-07-15

P/N: CTR-SPD24X2

CTR-SPD24X2 Dual 24V Pump Controller



CTR-SPD24X2 steps-up 12V computer voltage to 24V DC for 1-2 pumps. This allows Koolance [PMP-450](#) and [PMP-450S](#) pumps to operate closer to maximum specification. The controller provides independent manual speed adjustment from 10-24V DC up to 55W per pump. Housed in an anodized aluminum 5.25" bay enclosure. Dimensions are approximately 5.7" x 3.9" x 1.6" (14.5cm x 9.9cm x 4.1cm).

Two 3 to 4-pin pump adapters and mounting screws are included.

General	
Weight	0.80 lb (0.36 kg)