www.koolance.com

Specifications Sheet

Generated: 2026-11-11

P/N: VLV-10TSPL

Drain Valve for ID 10mm (3/8in)





Inline drain valve to expedite coolant evacuation without turning your unit upside-down. Nickel-plated brass.

To use, simply install the valve on a 10mm (3/8in), 13mm (1/2in) OD line near the bottom of your setup. When you need to empty the system, place a 1-Liter container below the valve and unscrew it. Next, open the top Koolance reservoir refill plug on your cooling system.

General	
Weight	0.19 lb (0.09 kg)
Max Pressure Tolerance @ 25°C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120°C (248°F)
Wetted Materials	Nickel-Plated Brass, EPDM

File





NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
KOOLANCE		UNIT MM	ITEM VLV-10TSPL	
	BY / BY / BY / APPRD BY	SCALE N/S	TITLE Ass'y	
DATE		3RD ANGLE		
	S.J.LEE	CODE NO.	DWG. NO.	PAGE

REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY
△					

REVISION