www.koolance.com

Specifications Sheet

Generated: 2026-11-02

P/N: CNT-VDA34-BK

Dual VID Connector, *Black* Adjustable 2-3 Slot Spacing





Adjustable direct connection fitting for supported Koolance VID coolers in series or parallel. CNT-VDA34-BK is for SLI or CrossFire setups that span four to five card slots (two to three in between are bypassed). Koolance VID water blocks occupy the same slot as the video card. See this page for more details.


G 1/4 BSPP threading, made of brass with compression fittings and gaskets. Will work with any hose diameter going in and out of the Koolance video coolers. To adjust, loosen the threaded center nut, slide apart, and re-tighten. Do not adjust sliding fittings beyond the marked safety line.

General	
Weight	0.11 lb (0.05 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	5kgf/cm2 (71.1psi)
Max Temperature Tolerance	100°C (212°F)

File







NO.	DESCRIPTION				MATER'L		QUANTITY	REMARKS
KOOLANCE					UNIT	MM	APPAR CNT-VDA34(-BK)	
	BY	BY	BY	APPRO BY	SCALE	N/S	TITLE Ass'y	
DATE					3RD ANGLE			
04/10/2017	S.J.LEE				CODE NO.		DWG. NO.	