www.koolance.com

Specifications Sheet

Generated: 2026-11-16

P/N: CNT-VDA2

Dual VID Connector, Adjustable 1 Slot Spacing





Adjustable direct connection fitting for supported Koolance VID coolers in series or parallel. CNT-VDA2 is for SLI or CrossFire setups that span three card slots (one in between is bypassed). Koolance VID water blocks occupy the same slot as the video card. See this page for more details.


G 1/4 BSPP threading, nickel-plated brass with compression fittings and gaskets. Will work with any hose diameter going in and out of the Koolance video coolers. To adjust, loosen the threaded center nut, slide apart, and re-tighten. Do not adjust sliding fittings beyond the safety line, marked "MAX".

General	
Weight	0.06 lb (0.03 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	5kgf/cm2 (71.1psi)
Max Temperature Tolerance	100°C (212°F)

File







NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT MM	APPAR CNT-VDA2(-BK)	
	BY	BY	BY	APPRO BY	SCALE N/S	TITLE Ass'y	
DATE					3RD ANGLE		
04/10/2017	S.J.LEE				CODE NO.	DWG. NO.	