

EX2-1050BK (Exos-2.5) Liquid Cooling System, Black



The Exos-2.5 possesses triple 120mm fans and an extended heat exchanger for approximately 1000W of cooling capacity. Its powerful [PMP-400](#) pump also better assists systems with multiple blocks, splitters, and other components that naturally reduce flow and pump pressure.

The Exos-2.5 features rear G 1/4 BSPP (parallel) thread inlet and outlet fitting sockets (fittings are not included). This allows any Koolance G 1/4 BSPP fitting or threaded quick-disconnect to be added to the unit. Like all Exos systems, the Exos-2.5 will connect with any PC through a standard rear card slot. This is ideal to avoid any modification to the computer chassis.

NOTE: The included Exos Slot Adapter will accommodate tubing up to 3/8in (10mm) ID, 1/2in (13mm) OD. If using 1/2in (13mm) ID tubing, Koolance recommends the [BKT-PCI-G](#) with your preferred fittings.

- Variable pump speed via the front display
- Rear G 1/4 BSPP inlet and outlet fitting sockets
- Radiator fan speeds adjust automatically, or with 10 manual levels
- Blue reservoir LED lighting
- Top coolant fill plug
- Independently-variable alarm and safety shutdown temperatures on all three sensors!
- Adapted power connection - does not require an AC power outlet
- Optional [attachment strap](#) for systems "on the go"

General	
Weight	7.40 lb (3.36 kg)
Cooling Systems	
Display Type	LED
Fans	3 x 120mm (269CFM)
Max Flow Rate (10-13mm ID)	PMP-400 @ 12V
Power Source	12 VDC
Radiator	Aluminum
Temperature Sensors	50K Thermistors

Koolance ERM-2K3U,
 Exos-2 / V2 / LX / 2.5 / LT V2
 Rear DB9 Pin-out



