



www.koolance.com

Specifications Sheet

Generated: 2024-04-20

P/N: FAN-14025HLED

Fan, 140x25mm, 91CFM, Blue LED



Koolance high quality, dual ball-bearing fan with blue LEDs.

- Dimensions: 140x140x25mm
- Type: Dual Ball-Bearing
- Connector: 3-pin (3-wire with tachometer)
- Rated Voltage: 12VDC
- Current: 0.2A
- Speed: 1700RPM (max)
- Static Pressure: 1.9mm-H2O
- Airflow: 91.2CFM (max)
- Noise: 36.3dBA (max)
- 50k hours MTBF

General	
Weight	0.40 lb (0.18 kg)
Noise (dBA)	36.3
Fans	
Airflow (CFM)	91.2
Current (A)	0.2
Size (mm)	140 x 140 x 25
Speed (RPM)	1700
Static Pressure (mm-H2O)	1700
Tachometer	yes
Voltage	12 VDC