



Koolance high quality, dual ball-bearing fan with blue LEDs.

- Dimensions: 140x140x25mm
- Type: Dual Ball-Bearing
- Connector: 3-pin (3-wire with tachometer)
- Rated Voltage: 12VDC
- Current: 0.2A
- Speed: 1700RPM (max)
- Static Pressure: 1.9mm-H2O
- Airflow: 91.2CFM (max)
- Noise: 36.3dBA (max)
- 50k hours MTBF

| General | |
|--------------------------|-------------------|
| Weight | 0.40 lb (0.18 kg) |
| Noise (dBA) | 36.3 |
| Fans | |
| Airflow (CFM) | 91.2 |
| Current (A) | 0.2 |
| Size (mm) | 140 x 140 x 25 |
| Speed (RPM) | 1700 |
| Static Pressure (mm-H2O) | 1700 |
| Tachometer | yes |
| Voltage | 12 VDC |