www.koolance.com

Specifications Sheet

Generated: 2026-11-04

P/N: FAN-14025HBK

Fan, 140x25mm, 91CFM



Koolance high quality, dual ball-bearing fan.

- Dimensions: 140x140x25mm
- Type: Dual Ball-Bearing
- Connector:3-pin (3-wire with tachometer)
- Rated Voltage: 12VDC
- Current: 0.20A
- Speed: 1700RPM (max)
- Static Pressure: 1.9mm-H2O
- Airflow: 91.2CFM (max)
- Noise: 36.3dBA (max)
- 50k hours MTBF

General	
Weight	0.40 lb (0.18 kg)
Noise (dBA)	36.3
Fans	
Airflow (CFM)	91.2
Current (A)	0.20
Size (mm)	140 x 140 x 25
Speed (RPM)	1700
Static Pressure (mm-H2O)	1.9
Tachometer	yes
Type	Dual Ball Bearing
Voltage	12 VDC