



- Momentary NO magnetic switches which activate when the float reaches their location.
- Contact Rating : 10VA max.
- Switching Voltage : DC/AC 100V max.
- Switching Current : 0.5A max.

REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY

REVISION

NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS

  

		UNIT	MM INCH	APPAR	SEN-LVL70
		SCALE	N/S	TITLE	70mm, 1 LEVEL SENSOR DIM
DATE	BY	BY	BY	APPRO BY	3RD ANGLE
	S.J.LEE				