



- Momentary NO magnetic switches which activate when the float reaches their location.
- Contact Rating : 10VA max.
- Switching Voltage : DC/AC 100V max.
- Switching Current : 0.5A max.

REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY

NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
		UNIT	MM INCH	APPAR SEN2-LVL70
		SCALE	N/S	TITLE
DATE	BY	BY	BY	APPRD BY
APR.20.2021	S.J.LEE			
3RD ANGLE			CODE NO.	DWG. NO.
70mm, 2 LEVEL SENSOR DIM				