www.koolance.com

Specifications Sheet

Generated: 2026-11-01

P/N: FIT-V10PC


Push-to-Connect Fitting for 3/8in (9.5mm) OD, G 1/4 BSPP




Koolance push-to-connect tube fitting for 3/8in (9.5mm) OD dense plastic tubing, G 1/4 BSPP thread. (Not for use with softer plastic materials, such as Koolance's PVC or PU tubing.) A toothed collet and dual o-rings secure tubing when inserted. To release tubing for removal, depress the outer ring.

General	
Weight	0.06 lb (0.03 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	8kgf/cm2 (113.8psi)
Max Temperature Tolerance	80°C (176°F)
Min Storage Temperature (*No Freezing)	-30ºC (-22ºF)
Wetted Materials	Brass, Nickel Plating, EPDM

File





NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE®					UNIT MM	APPAR FIT-V10PC	
	BY	BY	BY	APPRO. BY	SCALE N/S	TITLE Ass'y	
DATE					3RD ANGLE		
AUG.03.2022	S.J.LEE				CODE NO.	DWG. NO.	