

Barb Fitting for ID 03mm (1/8in), G 1/4 BSPP



Single barb fitting for 1/8in (3mm) ID tubing. G 1/4 BSPP (parallel) thread. Includes spring clamp for 5mm (3/16in) OD tubing.

General	
Weight	0.03 lb (0.01 kg)
Max Pressure Tolerance @ 25° C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120° C (248° F)
Wetted Materials	Nickel-Plated Brass, EPDM

