www.koolance.com

Specifications Sheet

Generated: 2026-11-03

P/N: FIT-V13G38


Barb Fitting for ID 13mm (1/2in), G 3/8 BSPP



Single barb fitting for 1/2in (13mm) ID tubing. G 3/8 BSPP (parallel) thread. Spring clamp for 5/8in (16mm) OD included.

General	
Weight	0.13 lb (0.06 kg)
Max Pressure Tolerance @ 25°C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120°C (248°F)
Wetted Materials	Brass, Nickel Plating, EPDM

File



NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
KOOLANCE		UNIT MM	ITEM FIT-V13G38	
		SCALE N/S	TITLE Ass'y	
	BY BY BY APPRD BY	DECIMAL PLACES 0 : ±0.3 0.X : ±0.1 0.XX : ±0.05		
DATE			DWG. NO.	PAGE
	SK.AN	CODE NO.		