www.koolance.com

Specifications Sheet

Generated: 2026-11-02

P/N: FIT-V13N12


Barb Fitting for ID 13mm (1/2in), 1/2 NPT



Single barb fitting for 1/2in (13mm) ID tubing. 1/2 NPT (tapered) thread. Spring clamp for 5/8in (16mm) OD included.

General	
Weight	0.19 lb (0.09 kg)
Max Pressure Tolerance @ 25°C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120°C (248°F)
Wetted Materials	Brass, Nickel Plating, EPDM

File



NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE®					UNIT MM	ITEM FIT-V13N12	
	BY	BY	BY	APPRD BY	SCALE N/S	TITLE Ass'y	
DATE					3RD ANGLE		
	S.J.LEE				CODE NO.	DWG. NO.	PAGE