www.koolance.com

Specifications Sheet

Generated: 2026-10-31

P/N: FIT-V13N38


Barb Fitting for ID 13mm (1/2in), 3/8 NPT



Single barb fitting for 1/2in (13mm) ID tubing. 3/8 NPT (tapered) thread. Spring clamp for 5/8in (16mm) OD included.

General	
Weight	0.14 lb (0.06 kg)
Max Pressure Tolerance @ 25°C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120°C (248°F)
Wetted Materials	Brass, Nickel Plating, EPDM

File



NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
KOOLANCE		UNIT MM	ITEM FIT-V13N38	
	BY BY BY APPRD BY	SCALE N/S	TITLE Ass'y	
DATE		3RD ANGLE		
	S.J.LEE	CODE NO.	DWG. NO.	PAGE