www.koolance.com

Specifications Sheet

Generated: 2026-11-03

P/N: FIT-V19N38


Barb Fitting for ID 19mm (3/4in), 3/8 NPT




Single barb fitting for 3/4in (19mm) ID tubing. 3/8 NPT (tapered) thread. Spring clamp for 7/8in (22mm) OD included.

General	
Weight	0.30 lb (0.14 kg)
Max Pressure Tolerance @ 25°C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120°C (248°F)
Wetted Materials	Brass, Nickel Plating

File





NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
KOOLANCE		UNIT MM	ITEM FIT-V19N38	
	BY BY BY APPRD BY	SCALE N/S	TITLE Ass'y	
DATE		3RD ANGLE		
	S.J.LEE	CODE NO.	DWG. NO.	PAGE