www.koolance.com

**Specifications Sheet**

Generated: 2026-11-02

# P/N: FIT-V06X10-BK


## Compression Fitting for 06mm x 10mm (1/4in x 3/8in) *Black*, G 1/4 BSPP




Single fitting for 1/4in (6mm) ID, 3/8in (10mm) OD tubing. G 1/4 BSPP (parallel) thread.

| General | |
|---|---|
| Weight | 0.04 lb (0.02 kg) |
| Max Pressure Tolerance @ 25°C | 15kgf/cm2 (213.4psi) |
| Max Temperature Tolerance | 120°C (248°F) |
| Wetted Materials | Brass, EPDM |

File




| REV | DATE | CONTENTS | REVD BY | CHKD BY | APPD BY |
|---|---|---|---|---|---|
| | | | | | |
| | | | | | |

REVISION

| NO. | DESCRIPTION | MATER'L | QUANTITY | REMARKS |
|---|---|---|---|---|
| KOOLANCE INC. | | UNIT MM | APPAR | FIT-V06X10(-BK) |
| | BY / BY / BY / APPRD BY | SCALE N/S | TITLE | Ass'y |
| DATE | | 3RD ANGLE | | |
| 05.01.2014 | S.J.LEE | REF. NO. | DWG. NO. | |