www.koolance.com

Specifications Sheet

Generated: 2026-11-11

P/N: FIT-V06X10


Compression Fitting for 06mm x 10mm (1/4in x 3/8in), G 1/4 BSPP



Single fitting for 1/4in (6mm) ID, 3/8in (10mm) OD tubing. G 1/4 BSPP (parallel) thread.

General	
Weight	0.04 lb (0.02 kg)
Max Pressure Tolerance @ 25°C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120°C (248°F)
Wetted Materials	Brass, Nickel Plating, EPDM

File



REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY

REVISION

NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
KOOLANCE INC.		UNIT MM	APPAR	FIT-V06X10(-BK)
	BY / BY / BY / APPRD BY	SCALE N/S	TITLE	Ass'y
DATE		3RD ANGLE		
05.01.2014	S.J.LEE	REF. NO.	DWG. NO.	