www.koolance.com

**Specifications Sheet**

Generated: 2026-11-14

# P/N: FIT-V10X13


## Compression Fitting for 10mm x 13mm (3/8in x 1/2in), G 1/4 BSPP




Single fitting for 3/8in (10mm) ID, 1/2in (13mm) OD tubing. G 1/4 BSPP (parallel) thread fitting.

| General | |
|---|---|
| Weight | 0.07 lb (0.03 kg) |
| Max Pressure Tolerance @ 25°C | 15kgf/cm2 (213.4psi) |
| Max Temperature Tolerance | 120°C (248°F) |
| Wetted Materials | Brass, Nickel Plating, EPDM |

File




| | | | | | |
|---|---|---|---|---|---|
| | | | | | |
| ⚠ | | | | | |
| ⚠ | | | | | |
| REV | DATE | CONTENTS | REVD BY | CHKD BY | APPD BY |

REVISION

| NO. | DESCRIPTION | | | | MATER'L | QUANTITY | REMARKS |
|---|---|---|---|---|---|---|---|
| KOOLANCE INC. | | | | | UNIT MM | APPAR | FIT-V10X13(-BK) |
| | BY | BY | BY | APPRD BY | SCALE N/S | TITLE | Ass'y |
| DATE | | | | | 3RD ANGLE | | |
| 05.01.2014 | S.J.LEE | | | | REF. NO. | DWG. NO. | |