www.koolance.com

Specifications Sheet

Generated: 2026-11-16

P/N: FIT-V10X16


Compression Fitting for 10mm x 16mm (3/8in x 5/8in), G 1/4 BSPP



Single fitting for 3/8in (10mm) ID, 5/8in (16mm) OD tubing. G 1/4 BSPP (parallel) thread fitting.

General	
Weight	0.09 lb (0.04 kg)
Max Pressure Tolerance @ 25°C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120°C (248°F)
Wetted Materials	Brass, Nickel Plating, EPDM

File



NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
KOOLANCE INC.		UNIT MM	APPAR	FIT-V10X16(-BK)
	BY BY BY APPRD BY	SCALE N/S	TITLE	Ass'y
DATE		3RD ANGLE		
05.01.2014	S.J.LEE	REF. NO.	DWG. NO.	

REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY
2					
1					

REVISION