www.koolance.com

Specifications Sheet

Generated: 2026-10-31

P/N: FIT-L13N14


Rotary Elbow Barb Fitting for 13mm (1/2in) ID, 1/4 NPT



Single rotational angled fitting for 1/2in (13mm) ID tubing. 1/4 NPT (tapered) thread. Tube clamp for 5/8in (16mm) OD included.

General	
Weight	0.13 lb (0.06 kg)
Max Pressure Tolerance @ 25°C	8kgf/cm2 (113.8psi)
Max Temperature Tolerance	100°C (212°F)
Wetted Materials	Brass, Nickel Plating, EPDM

File



NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT MM	APPAR FIT-L13N14	
	BY	BY	BY	APPRO BY	SCALE N/S	TITLE Ass'y	
DATE					3RD ANGLE		
JUN.02.2021	S.J.LEE				CODE NO.	DWG. NO.	