www.koolance.com

Specifications Sheet

Generated: 2026-11-17

P/N: FIT-L10X13N14


Rotary Elbow Compression Fitting for 10mm x 13mm (3/8in x 1/2in), 1/4 NPT





Single rotational angled fitting for 3/8in (10mm) ID, 1/2in (13mm) OD tubing. 1/4 NPT (tapered) thread.

General	
Weight	0.11 lb (0.05 kg)
Max Pressure Tolerance @ 25°C	8kgf/cm2 (113.8psi)
Max Temperature Tolerance	100°C (212°F)
Wetted Materials	Brass, Nickel Plating, EPDM

File







REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY

REVISION

NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
KOOLANCE INC.		UNIT MM	APPAR FIT-L10X13N14	
	BY BY BY APPRD BY	SCALE N/S	TITLE Ass'y	
DATE		3RD ANGLE		
	S.J.LEE	REF. NO.	DWG. NO.	