www.koolance.com

Specifications Sheet

Generated: 2026-11-15

P/N: FIT-L13X16N14


Rotary Elbow Compression Fitting for 13mm x 16mm (1/2in x 5/8in), 1/4 NPT





Single rotational angled fitting for 1/2in (13mm) ID, 5/8in (16mm) OD tubing. G 1/4 BSPP (parallel) thread.

General	
Weight	0.13 lb (0.06 kg)
Max Pressure Tolerance @ 25°C	8kgf/cm2 (113.8psi)
Max Temperature Tolerance	100°C (212°F)
Wetted Materials	Brass, Nickel Plating, EPDM

File







NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
KOOLANCE INC.		UNIT MM	APPAR FIT-L13X16N14	
	BY / BY / BY / APPRD BY	SCALE N/S	TITLE Ass'y	
DATE		3RD ANGLE		
	S.J.LEE	REF. NO.	DWG. NO.	

REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY

REVISION