www.koolance.com

Specifications Sheet

Generated: 2026-11-09

P/N: ADT-DXG90


Fitting Single, Swiveling 90-Degree, G 1/4 BSPP



Koolance swiveling G 1/4 BSPP socket fitting. Each segment rotates for a maximum 90-degree bend.

General	
Weight	0.13 lb (0.06 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	8kgf/cm2 (113.8psi)
Max Temperature Tolerance	100°C (212°F)
Wetted Materials	Brass, Nickel Plating, EPDM

File



NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT MM	APPAR ADT-DXG90	
	BY	BY	BY	APPRO BY	SCALE N/S	TITLE Ass'y	
DATE					3RD ANGLE		
04/06/2017	S.J.LEE				CODE NO.	DWG. NO.	