www.koolance.com

Specifications Sheet

Generated: 2026-10-31

P/N: FIT-L10G38


Rotary Elbow Barb Fitting for ID 10mm (3/8in), G 3/8 BSPP





Rotational angled fitting for 3/8in (10mm) ID tubing. G 3/8 BSPP (parallel) thread. Spring clamp for 1/2in (13mm) OD included.

General	
Weight	0.13 lb (0.06 kg)
Max Pressure Tolerance @ 25°C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120°C (248°F)
Wetted Materials	Brass, Nickel Plating, EPDM

File







NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
KOOLANCE		UNIT MM	APPAR FIT-L10G38	
	BY BY BY APPRD BY	SCALE N/S	TITLE Ass'y	
DATE		3RD ANGLE		
	SK.AN	CODE NO.	DWG. NO.	