

Rotary Elbow Barb Fitting for ID 10mm (3/8in),  
G 3/8 BSPP



Rotational angled fitting for 3/8in (10mm) ID tubing. G 3/8 BSPP (parallel) thread. Spring clamp for 1/2in (13mm) OD included.

General	
Weight	0.13 lb (0.06 kg)
Max Pressure Tolerance @ 25° C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120° C (248° F)
Wetted Materials	Brass, Nickel Plating, EPDM

