

Display For Flow Meter and Temperature Sensor



Flow meter and temperature sensor sold separately.

The DCB-FMTP01 can display the temperature and flow rate values from a Koolance 10K Ohm thermistor and flow meter (sold separately). It can also sound an audio alarm based on the flow rate or temperature. It requires 12VDC input power, and includes two different wiring harnesses.

The display is compatible with the below Koolance flow meter models, but can be configured for other custom pulse factors:

- INS-FM14
- INS-FM16
- INS-FM17H (hall effect)
- INS-FM17N
- INS-FM18
- INS-FM19
- SEN-FM18T10

A bracket is included to optionally mount the display directly to a Koolance flow meter. Due to size constraints, only certain models of Koolance flow meters and tube fittings are compatible with the bracket. These include flow meter models: INS-FM14, INS-FM17H, INS-FM17N, INS-FM18, and SEN-FM18T10. The bracket supports tube fittings on the flow meter with an outer diameter up to 22.4mm (0.88in). This includes Koolance barb fittings for tubing up to 13mm (1/2in) internal diameter, or Koolance compression fittings for tubing up to 13mm (1/2in) outer diameter.

General	
Weight	0.38 lb (0.17 kg)

