www.koolance.com

Specifications Sheet

Generated: 2026-11-22

P/N: GPU-180-L06


GPU-180-L06 Water Block (Video/Motherboard Chipset) [06mm, 1/4in ID]





Featuring a very efficient 200W patented design, the GPU-180-L06 has 360-degree rotational fittings to achieve a variety of mounting directions on video card or motherboard chipsets.

Created from high density solid copper and plated in gold, the GPU-180 includes a sliding mounting bracket to fit all types of chipset mounting holes. Two sizes of bracket tabs are included, plus mounting hooks for Intel chipsets and 8 aluminum self-adhesive video memory heat sinks.

General	
Weight	0.40 lb (0.18 kg)
Wetted Materials	Gold-Plated Copper, Engineering Resin, Silicone






Thermal Resistance vs. Pressure Drop
Thermal Resistance (℃/W)
0.15
0.13
0.11
0.09
0.07
0.05
0.0
1.0
2.0
3.0
4.0
5.0
6.0
7.0
8.0
Pressure Drop (psi)
GPU-180-L06