www.koolance.com

Specifications Sheet

Generated: 2026-11-11


P/N: HOS-10X17EP-3M

Hose, EPDM Black, Dia: 10mm x 17mm (3/8in x 11/16in) - [Length 3m / 9.8ft]



Koolance black EPDM thread-reinforced hose with 10mm (3/8in) internal diameter, 17mm (11/16in) external diameter. Length 3m / 9.8ft. Bend radius is approximately 35mm (1.38in).

General	
Weight	1.60 lb (0.73 kg)
Max Pressure Tolerance @ 25°C	7.1kgf/cm2 (101.5psi)
Max Temperature Tolerance	120°C (248°F)
Hardness (Shore)	70A



EPDM thread-reinforced

NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
KOOLANCE		UNIT inch	APPAR	
	BY / BY / BY / APPRD BY	SCALE N/S	TITLE HOS-10X17EP-XX	
DATE		3RD ANGLE		
2026.05.11	SK.An	CODE NO.	DWG. NO.	