



Koolance black EPDM thread-reinforced hose with 10mm (3/8in) internal diameter, 17mm (11/16in) external diameter. Length 100m / 328ft. Bend radius is approximately 35mm (1.38in).

General	
Weight	50.00 lb (22.68 kg)
Max Pressure Tolerance @ 25 °C	7.1kgf/cm ² (101.5psi)
Max Temperature Tolerance	120 °C (248 °F)
Hardness (Shore)	70A