



Koolance black EPDM thread-reinforced hose with 13mm (1/2in) internal diameter, 21mm (13/16in) external diameter. Length 3m / 9.8ft. Bend radius is approximately 50mm (1.97in).

General	
Weight	2.00 lb (0.91 kg)
Max Pressure Tolerance @ 25 °C	7.1kgf/cm <sup>2</sup> (101.5psi)
Max Temperature Tolerance	120 °C (248 °F)
Hardness (Shore)	70A

