



Koolance black EPDM thread-reinforced hose with 13mm (1/2in) internal diameter, 21mm (13/16in) external diameter. Length 50m / 164ft. Bend radius is approximately 50mm (1.97in).

General	
Weight	31.80 lb (14.42 kg)
Max Pressure Tolerance @ 25°C	7.1kgf/cm ² (101.5psi)
Max Temperature Tolerance	120°C (248°F)
Hardness (Shore)	70A