



Koolance black EPDM thread-reinforced hose with 16mm (5/8in) internal diameter, 24mm (15/16in) external diameter. Length 50m / 164ft. Bend radius is approximately 55mm (2.17in).

General	
Weight	39.20 lb (17.78 kg)
Max Pressure Tolerance @ 25°C	7.1kgf/cm <sup>2</sup> (101.5psi)
Max Temperature Tolerance	120°C (248°F)
Hardness (Shore)	70A