www.koolance.com

Specifications Sheet

Generated: 2026-11-17


P/N: HOS-16X24EP-50M


Hose Roll, EPDM Black, Dia: 16mm x 24mm (5/8in x 15/16in) - [Length 50m / 164ft]



Koolance black EPDM thread-reinforced hose with 16mm (5/8in) internal diameter, 24mm (15/16in) external diameter. Length 50m / 164ft. Bend radius is approximately 55mm (2.17in).

General	
Weight	39.20 lb (17.78 kg)
Max Pressure Tolerance @ 25°C	7.1kgf/cm2 (101.5psi)
Max Temperature Tolerance	120°C (248°F)
Hardness (Shore)	70A





EPDM thread-reinforced

NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT inch	APPAR	
	BY	BY	BY	APPRD BY	SCALE N/S	TITLE HOS-16X24EP-XX	
DATE					3RD ANGLE		
2026.05.11	SK.An				CODE NO.	DWG. NO.	