www.koolance.com

Specifications Sheet

Generated: 2026-11-16

P/N: HOS-06X13EP-3M


Hose, EPDM Black, Dia: 06mm x 13mm (1/4in x 1/2in) - [Length 3m / 9.8ft]




Koolance black EPDM thread-reinforced hose with 6mm (1/4in) internal diameter, 13mm (1/2in) external diameter. Length 3m / 9.8ft. Bend radius is approximately 30mm (1.18in).

General	
Weight	0.80 lb (0.36 kg)
Max Pressure Tolerance @ 25°C	7.1kgf/cm2 (101.5psi)
Max Temperature Tolerance	120°C (248°F)
Hardness (Shore)	70A

File





EPDM thread-reinforced

NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
KOOLANCE					UNIT inch	APPAR	
	BY	BY	BY	APPRD BY	SCALE N/S	TITLE HOS-06X13EP-XX	
DATE					3RD ANGLE		
2026.05.11	SK.An				CODE NO.	DWG. NO.	