www.koolance.com

Specifications Sheet

Generated: 2026-11-16

P/N: INS-FLTR04

INS-FLTR04 Inline Coolant Filter




All metal inline coolant filter for keeping accidental debris from damaging the pump or clogging other components. It includes a reusable stainless steel filter with a hole size of 0.85mm/sq.

G 1/4 BSPP sockets are provided on both sides, with one male and one female for easy installation into the inlet of a water block, pump, or heat exchanger. Nickel-plated brass and stainless steel mesh filter. The filter body can be unscrewed for cleaning.

General	
Weight	0.09 lb (0.04 kg)
Fitting Thread	G 1/4 BSPP
Max Pressure Tolerance @ 25°C	5kgf/cm2 (71.1psi)
Max Temperature Tolerance	70°C (158°F)
Wetted Materials	Nickel-Plated Brass, Stainless Steel, EPDM

File



NO.	DESCRIPTION				MATER'L		QUANTITY	REMARKS
KOOLANCE					UNIT	MM	APPAR INS-FLTR04	
	BY	BY	BY	APPRO. BY	SCALE	N/S	TITLE	
DATE					3RD ANGLE		Ass'y	
04/12/2017	S.J.LEE				CODE NO.		DWG. NO.	