



All metal inline coolant filter for keeping accidental debris from damaging the pump or clogging other components. It includes a reusable stainless steel filter with a hole size of 0.42mm/sq.

G 1/4 BSPP sockets are provided on both sides, with one male and one female for easy installation into the inlet of a water block, pump, or heat exchanger. Nickel-plated brass and stainless steel mesh filter. The filter body can be unscrewed for cleaning.

General	
Weight	0.09 lb (0.04 kg)
Fitting Thread	G 1/4 BSPP
Materials	Nickel-Plated Brass, Stainless Steel, EPDM
Max Pressure Tolerance @ 25 °C	5kgf/cm2 (71.1psi)
Max Temp. Operating Tolerance	70 °C (158 °F)

