




Barb Fitting for ID 06mm (1/4in), Stainless Steel, 1/4 NPT



Single barb fitting for 1/4in (6mm) ID tubing. 1/4 NPT (tapered) thread. Includes spring clamp for 3/8in (10mm) OD tubing.

General	
Weight	0.03 lb (0.01 kg)
Max Pressure Tolerance @ 25 °C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120 °C (248 °F)
Wetted Materials	SUS 316, EPDM



REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY
△					
REVISION					

NO.	DESCRIPTION				MATER'L		QUANTITY	REMARKS
	KOLANCE				UNIT	MM	ITEM	FIT-V06N14-SS
					SCALE	N/S	TITLE	NPT 1/4 6mm 호스바브 노즐
DATE	BY	BY	BY	APPRO BY	3RD ANGLE		CODE NO.	DWG. NO.
	ys.shin						-	-
								PAGE