





Single hose barb fitting for 1/4in (6mm) ID tubing. G 1/4 BSPP (parallel) thread. Includes hose clamp for 3/8in (10mm) OD tubing.

General	
Weight	0.03 lb (0.01 kg)
Materials	SUS 316, EPDM
Max Pressure Tolerance @ 25 °C	15kgf/cm <sup>2</sup> (213.4psi)
Max Temp. Operating Tolerance	120 °C (248 °F)



REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY
REVISION					

NO.	DESCRIPTION				MATER'L	QUANTITY	REMARKS
<b>KOLANCE</b>					UNIT	MM	ITEM FIT-V06B-SS
					SCALE	N/S	TITLE
					6mm G-나사 호스바브 니플		
DATE	BY	BY	BY	APPRO BY	3RD ANGLE		
					CODE NO.	DWG. NO.	PAGE
					-		