www.koolance.com

**Specifications Sheet**

Generated: 2026-11-09

# P/N: FIT-V10B-SS


## Barb Fitting for ID 10mm (3/8in), Stainless Steel, G 1/4 BSPP




Single barb fitting for 3/8in (10mm) ID tubing. G 1/4 BSPP (parallel) thread. Spring clamp included for 1/2in (13mm) OD tubing.

| General | |
|---|---|
| Weight | 0.03 lb (0.01 kg) |
| Max Pressure Tolerance @ 25°C | 15kgf/cm2 (213.4psi) |
| Max Temperature Tolerance | 120°C (248°F) |
| Wetted Materials | SUS 316, EPDM |

File




| NO. | DESCRIPTION | MATER'L | QUANTITY | REMARKS |
|---|---|---|---|---|
| KOOLANCE | | UNIT MM | ITEM FIT-V10B-SS | |
| | BY / BY / BY / APPRD BY | SCALE N/S | TITLE 10mm G나사 호스바브 니쁠 | |
| DATE | | 3RD ANGLE | | |
| | ys.shin | CODE NO. | DWG. NO. — | PAGE |

| REV | DATE | CONTENTS | REVD BY | CHKD BY | APPD BY |
|---|---|---|---|---|---|

REVISION