www.koolance.com

Specifications Sheet

Generated: 2026-11-03

P/N: FIT-V13N14-SS


Barb Fitting for ID 13mm (1/2in), Stainless Steel, 1/4 NPT





Single barb fitting for 1/2in (13mm) ID tubing. 1/4 NPT (tapered) thread. Spring clamp is included for 5/8in (16mm) OD tubing.

General	
Weight	0.07 lb (0.03 kg)
Max Pressure Tolerance @ 25°C	15kgf/cm2 (213.4psi)
Max Temperature Tolerance	120°C (248°F)
Wetted Materials	SUS 316, EPDM

File







NO.	DESCRIPTION	MATER'L	QUANTITY	REMARKS
KOOLANCE		UNIT MM	ITEM FIT-V13N14-SS	
	BY / BY / BY / APPRD BY	SCALE N/S	TITLE NPT 1/4 13mm 호스바브 노즐	
DATE		3RD ANGLE		
	ys.shin	CODE NO.	DWG. NO. –	PAGE

REV	DATE	CONTENTS	REVD BY	CHKD BY	APPD BY
		REVISION			